



100 MM (4") PFA LED WAFER CARRIER

Secure protection for LED wafers


Overview

Entegris' new 100 mm (4") PFA wafer carrier is engineered based on the unique needs of the LED industry. Its all-PFA construction is inert to harsh chemical processes. In addition, the 100 mm (4") carrier is designed with wash openings for more effective drying at the end of your process and will prevent the retention of chemicals.

LED wafer manufacturers can rely on Entegris' proven quality based on 30+ years of wafer handling experience.

Features

- Unique robotic interface
- "H" bar equipment interface
- Both end walls have flanges that extend to bottom of the carrier
- Laser marking and RFID identification options
- Capacity: 25 wafers



Ordering Information

Part Number	Wafer Size	D1 Dimension	Pocket Spacing	Pocket Flat	Material
A72-40MBL-0215	100 mm (4")	13.97 mm (0.55")	4.76 mm (0.55")	1.52 mm (0.06")	PFA

For More Information

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit www.entegris.com and select the "Customer Service" link for the center nearest you.

Terms and Conditions of Sale

All purchases are subject to Entegris' "Terms and Conditions of Sale." To view and print this information, visit Entegris' website at www.entegris.com and select the Legal Notices link from the footer found on the home page.

Entegris® is a registered trademark of Entegris, Inc.

ENTEGRIS, INC.

Corporate Headquarters | 129 Concord Road | Billerica, MA 01821 USA
 Customer Service Tel. +1 952 556 4181 | Customer Service Fax +1 952 556 8022
 In North America 800 394 4083 | www.entegris.com

