



## WAFERGARD® III NF MICRO XL IN-LINE GAS FILTERS

*Superior particulate filtration for  
ultrapure gas system filtration*

### Overview

Wafergard® III nickel filters are the cleanest, most efficient all-metal filters available. The patented nickel filter membrane offers superior corrosion resistance and excellent compatibility with inert and reactive gases.\*

A state-of-the-art housing assembly eliminates outgassing by minimizing weld area. The all-metal construction is ideal for high-temperature and dynamic-pressure applications. Its compact size and flexible choice of fittings provide ultimate design efficiency and minimize engineering costs.


\*Not recommended for use with CO, O<sub>3</sub> and low-level hydride dopant gases.

### Applications


- Ultrapure gas lines
- High-temperature applications
- New fab construction
- Dynamic-pressure applications
- Inert and reactive gases

### Dimensions

WG3N S8 RR2/WG3N S8 RR2P



WG3N S8 SL2



### Ordering Information

Part Number	Description	Overall Length
WG3N S8 RR2	Wafergard III NF Micro XL in-line filter, 1/4" Gasket seal (compatible with VCR fitting) male inlet/outlet	84.1 mm (3.31")
WG3N S8 RR2P*	Wafergard III NF Micro XL in-line filter, 1/4" Gasket seal (compatible with VCR fitting) male inlet/outlet	84.1 mm (3.31")
WG3N S8 SL2	Wafergard III NF Micro XL in-line filter, 1/4" Gasket seal (compatible with VCR fitting) male inlet/outlet, short version	50.8 mm (2.00")

\*Fitting is protected with plastic cap instead of metallic cap




### Key Features

- Superior corrosion resistance
- Cleanest, most efficient filter

## Specifications

Materials:	Filter element	Patented, sintered nickel membrane filter	
	Housing	Electropolished VAR316L stainless steel housing	
Downstream cleanliness:	Particles	<0.03 particles/liter (<1 particle/ft <sup>3</sup> ) >0.01 μm	
	Volatiles	Volatile outgassing of H <sub>2</sub> O, O <sub>2</sub> and THC is below detectable limits (by RGA and FID at room temperature)	
Removal rating:	≥0.003 μm		
Surface finish interior:	≤5 μin Ra		
Helium leak rating:	Qualified	2 × 10 <sup>-10</sup> atm-cc/sec.	
	Tested	1 × 10 <sup>-9</sup> atm-cc/sec.	
Maximum operating conditions:	Maximum inlet pressure	20 MPa (200 bar, 2900 PSID) at 20°C	
	Maximum forward/reverse differential pressure	1 MPa (10 bar, 150 PSID)	
	Maximum operating temperature	Inert gases	400°C (725°F) @ 35 bar (500 PSI)
		Corrosive and reactive gases	50°C (122°F) @ 70 bar (1000 PSI)
Warranty:	5 year		
Particle retention:	Greater than 99.999999% (9 LRV) removal of all particles at 15 SLPM		
Flow rating:	Refer to performance data		

## Performance Data



## For More Information

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit [www.entegris.com](http://www.entegris.com) and select the "Customer Service" link for the center nearest you.

## Terms and Conditions of Sale

All purchases are subject to Entegris' "Terms and Conditions of Sale." To view and print this information, visit Entegris' website at [www.entegris.com](http://www.entegris.com) and select the Legal Notices link from the footer found on the home page.

Entegris® and Wafergard® are registered trademarks of Entegris, Inc. VCR® is a registered trademark of Swagelok Company.

### ENTEGRIS, INC.

Corporate Headquarters / 3500 Lyman Boulevard / Chaska, Minnesota 55318 USA  
 Customer Service Tel. 952-556-4181 / Customer Service Fax 952-556-8022  
[www.entegris.com](http://www.entegris.com)