

Fluorogard® FP Cartridge Filters

Providing filtration in gas applications


SPECIFICATIONS

Materials	Membrane	PTFE
	Support, core, sleeve	Polypropylene
	O-ring	EPDM (Size: AS568-222)
	Gasket	EPDM
Retention rating	0.003 µm for gas	
	0.2 µm for liquid	
Maximum forward/reverse differential pressure	0.34 MPa @ 25°C (77°F)	
Maximum operating temperature	30°C (86°F) in CDA and inert gases	
Recommended flow rate @ 25°C (77°F, 101 kPa)	10"	1500 L/min
	20"	3000 L/min
	30"	3600 L/min




DIMENSIONS

Code 0 (O-ring Seal Type)



Length	A
10"	245 mm (9.65")
20"	489 mm (19.25")
30"	733 mm (28.86")


Code F (Gasket Seal Type)




Length	A
10"	246 mm (9.69")
20"	487 mm (19.17")
30"	731 mm (28.78")

PERFORMANCE DATA


Fluorogard FP 10" Filters



Fluorogard FP 30" Filters




Fluorogard FP 20" Filters



ORDERING INFORMATION

Fluorogard FP PTFE Cartridge Filters: part number



FOR MORE INFORMATION

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit entegris.com and select the Contact Us link to find the customer service center nearest you.

TERMS AND CONDITIONS OF SALE

All purchases are subject to Entegris' Terms and Conditions of Sale. To view and print this information, visit entegris.com and select the Terms & Conditions link in the footer.



Corporate Headquarters
129 Concord Road
Billerica, MA 01821
USA

Customer Service
Tel +1 952 556 4181
Fax +1 952 556 8022
Toll Free 800 394 4083

Entegris®, the Entegris Rings Design™, Pure Advantage™, and other product names are trademarks of Entegris, Inc. as listed on entegris.com/trademarks. All third-party product names, logos, and company names are trademarks or registered trademarks of their respective owners. Use of them does not imply any affiliation, sponsorship, or endorsement by the trademark owner.

©2016-2017 Entegris, Inc. | All rights reserved. | Printed in the USA | 4419-8120ENT-1217