



FLUOROGARD® FP CARTRIDGE FILTERS

Providing filtration in gas applications


Specifications

Materials:	Membrane	PTFE
	Support, core, sleeve	Polypropylene
	O-ring	EPDM (Size: AS568-222)
	Gasket	EPDM
Retention rating:	0.003 µm for gas	
	0.2 µm for liquid	
Maximum forward/reverse differential pressure:	0.34 MPa @ 25°C (77°F)	
Maximum operating temperature:	90°C (194°F)	
Recommended flow rate @ 25°C (77°F, 101 kPa)	10"	1500 L/min
	20"	3000 L/min
	30"	3600 L/min




Dimensions

Code O (O-ring Seal Type)






Length	Dimension A
10"	245 mm (9.65")
20"	489 mm (19.25")
30"	733 mm (28.86")

Code F (Gasket Seal Type)



Length	Dimension A
10"	246 mm (9.69")
20"	487 mm (19.17")
30"	731 mm (28.78")


Performance Data



Ordering Information

Fluorogard FP PTFE Cartridge Filters

Part Number



For More Information

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit www.entegris.com and select the Customer Service link for the center nearest you.

Terms and Conditions of Sale

All purchases are subject to Entegris' Terms and Conditions of Sale. To view and print this information, visit www.entegris.com and select the Legal Notices link from the footer.

Entegris®, the Entegris Rings Design®, Creating a Material Advantage® and Fluorogard® are registered trademarks of Entegris, Inc.

ENTEGRIS, INC.

Corporate Headquarters | 129 Concord Road | Billerica, MA 01821 USA
 Customer Service Tel. +1 952 556 4181 | Customer Service Fax +1 952 556 8022
 In North America 800 394 4083 | www.entegris.com