

# Linegard™ MAX-FP Gas Filters

*Cost-effective 0.0015 µm filters for mid-flow range, noncritical applications*

Linegard™ MAX-FP in-line gas filters have a particle removal rating of  $\geq 0.0015\ \mu\text{m}$  and are a cost-effective solution for mid-flow range, noncritical applications. Recommended for filtration of compressed dry air and inert gases such as general nitrogen in instrument air, air knife, purge/vent line, hook up, and dryer applications.



*Linegard™ MAX-FP gas filters for mid-flow range applications*

## APPLICATIONS

- Mid-flow range on noncritical applications
- For filtration of compressed dry air and inert gases
- Instrument air, air knife, purge/vent line, hook up and dryer

## FEATURES & BENEFITS

<b>PTFE membrane supported by polypropylene structures</b>	Provides a cost-effective solution for filtration of compressed air and inert gases
<b>Compact housing with large diameter filter element</b>	Enables high flow rate/low pressure drop, resulting in up to 1000 slpm
<b>Various fitting and length configurations</b>	Provide easy installation without requiring gas panel or delivery system design changes


# SPECIFICATIONS

Materials	Membrane: PTFE
	Supports: Polypropylene
	O-Ring: Fluoroelastomer (FKM)
	Housing: 316L stainless steel
Surface finish interior	25 µin Ra
Removal rating	≥0.0015 µm (in gas)
Maximum operating conditions	Maximum inlet pressure: 0.7 MPa (7 bar, 101.5 psig) @ RT
	Maximum forward differential pressure: 0.41 MPa (4.1 bar, 59 psid) @ RT
	Maximum reverse differential pressure: 0.2 MPa (2 bar, 29 psid) @ RT
	Maximum operating temperature: 60°C (140°F)
Helium leak rating	1 x 10 <sup>-10</sup> Pa•m <sup>3</sup> /sec
Recommended gases	Compressed dry air (CDA) and inert gases
Warranty	1 year


For compatibility with other gases, please contact Entegris.

# PERFORMANCE DATA


Lineagard MAX-FP Filters with ¼" Fittings (except NPT)




Lineagard MAX-FP Filters with ⅜" Fittings and ¼" NPT



Lineagard MAX-FP Filters with ½" Fittings



## DIMENSIONS



Part number	Fitting	Length (L)
LGMXFPSS2	1/4" Swagelok compatible	112.7 mm (4.44")
LGMXFPSS2L	1/4" Swagelok compatible (long)	141.0 mm (5.55")
LGMXFPSS3	3/8" Swagelok compatible	117.9 mm (4.64")
LGMXFPSS3L	3/8" Swagelok compatible (long)	148.0 mm (5.83")
LGMXFPSS4	1/2" Swagelok compatible	118.7 mm (4.67")
LGMXFPRR2	1/4" Male VCR compatible	127.0 mm (5.00")
LGMXFPRR4	1/2" Male VCR compatible	127.0 mm (5.00")
LGMXFPBB2	1/4" Female NPT	131.8 mm (5.19")

## ORDERING INFORMATION

PART NUMBER	FITTING SIZE & TYPE
LGMXFPBB2	1/4" female NPT
LGMXFPRR2	1/4" male VCR® compatible
LGMXFPRR4	1/2" male VCR® compatible
LGMXFPSS2	1/4" Swagelok® compatible
LGMXFPSS2L	1/4" Swagelok® compatible (long length)
LGMXFPSS3	3/8" Swagelok® compatible
LGMXFPSS3L	3/8" Swagelok® compatible (long length)
LGMXFPSS4	1/2" Swagelok® compatible

#### FOR MORE INFORMATION

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit [entegris.com](http://entegris.com) and select the [Contact Us](#) link to find the customer service center nearest you.

#### TERMS AND CONDITIONS OF SALE

All purchases are subject to Entegris' Terms and Conditions of Sale. To view and print this information, visit [entegris.com](http://entegris.com) and select the [Terms & Conditions](#) link in the footer.



Corporate Headquarters  
129 Concord  
Billerica, MA 01821  
USA

Customer Service  
Tel +1 952 556 4181  
Fax +1 952 556 8022  
Toll Free 800 394 4083

Entegris®, the Entegris Rings Design®, and other product names are trademarks of Entegris, Inc. as listed on [entegris.com/trademarks](http://entegris.com/trademarks). All third-party product names, logos, and company names are trademarks or registered trademarks of their respective owners. Use of them does not imply any affiliation, sponsorship, or endorsement by the trademark owner.

©2009-2021 Entegris, Inc. | All rights reserved. | Printed in the USA | 4524-5786-1221

[www.entegris.com](http://www.entegris.com)