

Planarcap® NMB Filter

*Ultra-high particle loading capacity,
superior hard particle removal
capabilities, and gel retention
performance*

Planarcap® NMB filters offer an innovative solution for best-in-class, point-of-dispense slurry filtration with ultra-high particle loading capacity in sub-45 nm technology nodes. The advanced nanofiber continuous melt-blown (NMB) media technology enables superior hard particle removal and gel retention performance in CMP processes, reducing micro-scratches and extending filter lifetime. Planarcap NMB filters can be strategically installed at the final dispense point just before the slurry makes contact with the wafer.



Available in 73 mm or 89 mm outside diameters, and 5" or 2.5" lengths.

APPLICATIONS

- Chemical mechanical planarization (CMP) processes

FEATURES & BENEFITS


Nanofiber continuous melt-blown media technology	Enables superior agglomerate and gel removal
	Reduces microscratches
	Extends filter lifetime
Point-of-dispense design	Provides best-in-class slurry filtration prior to slurry dispense onto the wafer

SPECIFICATIONS


Materials of construction	Membrane, sleeve, core, shell	Polypropylene
Retention rating	Ø73 mm	A7, 01, 02, 05
	Ø89 mm	A5, A7, 01, 02, 05, 07, 10, 30, 50
Fitting connection	Inlet/outlet	3/8" or 1/4" Flaretek® fitting
	Vent/drain	1/4" Flaretek fitting or 1/8" MNPT
Maximum operating conditions	Maximum forward differential pressure	0.4 MPa @ 25°C (77°F)
	Maximum reverse pressure	0.2 MPa @ 25°C (77°F)
	Maximum operating temperature	60°C (140°F)

PERFORMANCE DATA


Planarcap NMB 2.5" Disposable Filters with
1/4" Inlet/Outlet Fitting (Ø73 mm)




Planarcap NMB 5" Disposable Filters with
1/4" Inlet/Outlet Fitting (Ø73 mm)



Planarcap NMB 2.5" Disposable Filters with
1/4" Inlet/Outlet Fitting (Ø89 mm)




Planarcap NMB 5" Disposable Filters with
1/4" Inlet/Outlet Fitting (Ø89 mm)




DIMENSIONS

2.5" Disposable, Ø73 mm




5" Disposable, Ø73 mm




Ø73 mm	2.5"		5"	
	A	B	A	B
1/4" Flaretek	98 mm (3.86")	152 mm (5.98")	153 mm (6.02")	208 mm (8.19")
3/8" Flaretek	98 mm (3.86")	152 mm (5.92")	153 mm (6.02")	208 mm (8.19")

2.5" Disposable, Ø89 mm



5" Disposable, Ø89 mm



Ø89 mm	2.5"		5"	
	A	B	A	B
1/4" Flaretek	98 mm (3.86")	152 mm (5.98")	153 mm (6.02")	206 mm (8.11")

DIMENSIONS

3/8" Flaretek

98 mm (3.86")

152 mm (5.98")


153 mm (6.02")

206 mm (8.11")

ORDERING INFORMATION

Planarcap NMB Point-of-Dispense CMP Filter: part number

P C B



* Ø89 mm only

** 1/4" Flaretek inlet/outlet only

FOR MORE INFORMATION

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit entegris.com and select the [Contact Us](#) link to find the customer service center nearest you.

TERMS AND CONDITIONS OF SALE

All purchases are subject to Entegris' Terms and Conditions of Sale. To view and print this information, visit entegris.com and select the [Terms & Conditions](#) link in the footer.



Corporate Headquarters
129 Concord
Billerica, MA 01821
USA

Customer Service
Tel +1 952 556 4181
Fax +1 952 556 8022
Toll Free 800 394 4083

Entegris®, the Entegris Rings Design®, and other product names are trademarks of Entegris, Inc. as listed on entegris.com/trademarks. All third-party product names, logos, and company names are trademarks or registered trademarks of their respective owners. Use of them does not imply any affiliation, sponsorship, or endorsement by the trademark owner.

©2016-2022 Entegris, Inc. | All rights reserved. | Printed in the USA | 4423-8255DSA-1022

www.entegris.com