

Pumpgard™ II Filter

*Protects wet station chemical pumps
from wafer particles*

Pumpgard™ II filters protect chemical pumps and final filters against damage caused by silicon wafer pieces. The 60 µm retention rating is ideal for capturing larger wafer pieces before they reach the pump and/or final filter.

Within the normal operation of a wet bench, process wafer can break and release wafer shards into the process bath. These shards can damage the bellows (made of fluoro-polymer resin) or the diaphragms within the pump.

Pumpgard II filters, installed on the upstream side of the recirculation pump, can efficiently remove shards from process chemical baths before damage occurs to expensive chemical pumps.

APPLICATIONS

- Semiconductor, flat panel display, data storage
- Point-of-tool, wet etch and clean and cleaning processes
- Aggressive acids, aggressive bases, solvents, resist strippers

FEATURES & BENEFITS


Fluoropolymer construction	Provides excellent compatibility with most acids, bases, and nonflammable solvents used in web stations
Large pore size	Ensures optimum process bath flow with minimum pressure drop, reducing downtime and eliminating risk of damage to expensive pumps
Compact design	Allows installation into new and existing pumps
	Ensures low hold-up of process chemicals, facilitating fast filter changeout while minimizing downtime and lowering operation costs



SPECIFICATIONS


Materials	Filter	PFA net
	Housing	440 HP PFA
Retention rating	60 μm	
Filtration area	23 cm^2 (3.5 in^2)	
Inlet/outlet connections	3/4" tube	
	3/4" Flaretek [®] fitting	
	1" Flaretek fitting	
Maximum operating conditions	Maximum input pressure	0.345 MPa (3.45 bar, 50 psi) at 25°C (77°F)
	Maximum forward/reverse differential pressure	0.345 MPa (3.45 bar, 50 psid) at 25°C (77°F)
	Maximum operating temperature	3/4": 180°C (356°F) at 14 psi
		1": 180°C (356°F) at 10 psi

PERFORMANCE DATA




DRAWINGS


3/4" Flaretek Fittings



1" Flaretek Fittings



3/4" Butt Weld Fittings



ORDERING INFORMATION

PART NUMBER	LENGTH	CONNECTION
WDPM0CP0F	5"	3/4" Flaretek® fitting
WDPM0CP4F	5"	1" Flaretek® fitting
WDPM0CPSF	7"	3/4" tube fitting

ORDERING INFORMATION

PART NUMBER	LENGTH	CONNECTION
WDPM0CPST3	7"	3/4" Super 300 type Pillar® fitting
WDPM0CPSTP	7"	3/4" Super type Pillar® fitting

FOR MORE INFORMATION

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit entegris.com and select the [Contact Us](#) link to find the customer service center nearest you.

TERMS AND CONDITIONS OF SALE

All purchases are subject to Entegris' Terms and Conditions of Sale. To view and print this information, visit entegris.com and select the [Terms & Conditions](#) link in the footer.



Corporate Headquarters
129 Concord
Billerica, MA 01821
USA

Customer Service
Tel +1 952 556 4181
Fax +1 952 556 8022
Toll Free 800 394 4083

Entegris®, the Entegris Rings Design®, and other product names are trademarks of Entegris, Inc. as listed on entegris.com/trademarks. All third-party product names, logos, and company names are trademarks or registered trademarks of their respective owners. Use of them does not imply any affiliation, sponsorship, or endorsement by the trademark owner.

©2011-2022 Entegris, Inc. | All rights reserved. | Printed in the USA | 4421-6194ENT-0522