

Wafergard® II SF Micro XL In-line Gas Filters

*Superior particulate filtration for
ultrapure gas system filtration*

Wafergard® II SF Micro XL gas filters are the filters of choice for high-purity gas systems when all stainless steel construction is preferred.

A state-of-the-art housing assembly eliminates outgassing by minimizing weld area. The all-metal construction is ideal for high-temperature and dynamic pressure applications. Its compact size and flexible choice of fittings provide ultimate design efficiency and minimizes engineering costs.



APPLICATIONS


- Ultra-high purity gas lines
- High-temperature applications
- New fab construction
- Dynamic pressure applications
- Inert and reactive gases

FEATURES & BENEFITS


- All-metal welded filter
- Excellent compatibility with most high-purity semiconductor process gases

DIMENSIONS


SI2R15E05 and WG2SS8RR2



SI2R19E07




SI2R20E08



SPECIFICATIONS

Materials	Filter element	Stainless steel membrane filter
	Housing	Electropolished VAR316L stainless steel housing
Downstream cleanliness	Particles	<0.03 particles/liter (<1 particle/ft ³) >0.01 μm
	Volatiles	<10 ppb moisture
Removal rating	≥0.0015 μm	
Surface finish interior	≤5.00 μin Ra	
Helium leak rating	Qualified	2 × 10 ⁻¹⁰ atm/cc-sec
	Tested	1 × 10 ⁻⁹ atm/cc-sec
Maximum operating conditions	Maximum inlet pressure: 20 MPa (200 bar; 2900 psi) @ 20°C (68°F)	
	Maximum forward/reverse differential pressure: 1 MPa (10 bar; 150 psid)	
	Maximum operating temperature: 460°C (860°F) @ 35 bar (500 psi)	
Warranty	2 years	
Particle retention	Greater than 99.9999999% (9 LRV) removal of all particles	
Flow rating	Refer to performance data	

PERFORMANCE DATA



ORDERING INFORMATION

Part number	Description	Length
SI2R15E05	Wafergard II SF Micro XL in-line gas filters, 1/4" gasket seal (compatible with VCR® fitting), male inlet/outlet	84.1 mm (3.31")
SI2R19E07	Wafergard II SF Micro XL in-line gas filters, 1/4" gasket seal (compatible with VCR fitting), female inlet/outlet, short version	50.8 mm (2.00")
SI2R20E08	Wafergard II SF Micro XL in-line gas filters, 1/4" gasket seal (compatible with VCR fitting), male inlet/outlet, short version	50.8 mm (2.00")
WG2SS8RR2	Wafergard SF Micro XL in-line gas filters, 1/4" gasket seal (compatible with VCR fitting), male inlet/outlet	84.1 mm (3.31")

FOR MORE INFORMATION

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit entegris.com and select the [Contact Us](#) link to find the customer service center nearest you.

TERMS AND CONDITIONS OF SALE

All purchases are subject to Entegris' Terms and Conditions of Sale. To view and print this information, visit entegris.com and select the [Terms & Conditions](#) link in the footer.



Corporate Headquarters

129 Concord Road
Billerica, MA 01821
USA

Customer Service

Tel +1 952 556 4181
Fax +1 952 556 8022
Toll Free 800 394 4083

Entegris®, the Entegris Rings Design®, and other product names are trademarks of Entegris, Inc. as listed on entegris.com/trademarks. All third-party product names, logos, and company names are trademarks or registered trademarks of their respective owners. Use of them does not imply any affiliation, sponsorship, or endorsement by the trademark owner.

©2009-2020 Entegris, Inc. | All rights reserved. | Printed in the USA | 4502-5451ENT-0820