GateKeeper® HGU Heated Getter Purifiers

Nitrogen and methane impurity removal for point-of-use purification of argon, helium, xenon, nitrogen, and hydrogen

GateKeeper® Heated Getter Units (HGU) are ideal solutions for point-of-use purification where CH_4 or N_2 impurity removal is required. Gases purified include Ar, He, Xe, N_2 , and H_2 .

The heated getter technology forms an irreversible bond with the impurities and removes them to sub-ppb levels. Unlike ambient purification technologies that rely on surface sorption only, heated getter technology utilizes the entire volume of material resulting in superior impurity capacity and longer purifier life.



- Vapor deposition processes
 - MOCVD
 - PVD
 - CVD
 - Epitaxy
- Photolithography
- Metrology
- R&D laboratory experiments
- LED

- Crystal pulling
- Implant
- Etching
- Diffusion and oxidation processes
- Annealing
- Fiber optics
- Analytical
- Solar and photovoltaics









PS4-MT3 and PS4-MT15 (left); PS4-MT50 (right)



PS2-GC50: Typical Flow Rate 0-0.2 slpm

SPECIFICATIONS

Maximum flow rate	0.2 slpm (nitrogen, helium, argon)
Outlet gas temperature	<50°C (122°F)
Average power consumption	<50 W
Metal particle filter	20 μm
Dimensions	Height: 23 cm (9") Width: 10 cm (4")
Weight	1.8 kg (4 lbs)
Standard features	1/4" VCR fittings
Optional features	110 – 120 VAC or 220 – 240 VAC

PERFORMANCE DATA

Impurities removed	Nitrogen outlet purity	Rare gas outlet purity
H ₂ O	<10 ppb	<10 ppb
O ₂	<10 ppb	<10 ppb
СО	<10 ppb	<10 ppb
CO ₂	<10 ppb	<10 ppb
CH ₄	<50 ppb	<10 ppb
Other hydrocarbons	<10 ppb	<10 ppb
H ₂	<10 ppb	<10 ppb
N ₂	N/A	<10 ppb

PS3-MT3: Typical Flow Rate 0.2-3 slpm

SPECIFICATIONS

Maximum flow rate	5 slpm (nitrogen, helium, argon)
	3 slpm (xenon)
Outlet gas temperature	<50°C (122°F)
Average power consumption	<50 W
Metal particle filter	0.003 μm
Dimensions	Height: 60 cm (24")
	Width: 25 cm (10")
	Depth: 10 cm (4")
Weight	6 kg (13 lbs)
Optional features	110 – 120 VAC or 220 – 240 VAC
	Bypass assembly (Part number BYPS-3)

PERFORMANCE DATA

Impurities removed	Nitrogen outlet purity	Rare gas outlet purity
H ₂ O	<1 ppb	<1 ppb
O_2	<1 ppb	<1 ppb
СО	<1 ppb	<1 ppb
CO ₂	<1 ppb	<1 ppb
CH ₄	<1 ppb	<1 ppb
Other hydrocarbons	<1 ppb	<1 ppb
H ₂	<1 ppb	<1 ppb
N ₂	N/A	<1 ppb

PS4-MT3 and PS4-MT15: Typical Flow Rate 3 – 30 slpm

SPECIFICATIONS

Optional

features

PERFORMANCE DATA

	МТЗ	MT15	
Average flow rate	5 slpm	15 slpm	
Maximum flow rate	50 slpm (nitrogen, helium, argon)	75 slpm (nitrogen, helium, argon)	
	30 slpm (hydrogen)	50 slpm (hydrogen	
	3 slpm (xenon)	9 slpm (xenon)	
Outlet gas temperature	<50°C (122°F)		
Average power consumption	125 W	187 W	
Metal particle filter	0.003 μm		
Dimensions	Height: 86.4 cm (34")		
	Width: 20.3 cm (8") Depth: 20.9 – 22.7 cm (8.25" – 8.94")		
Weight	23 – 28 kg (50 – 61 lbs)		
Standard	High temperature alarm		
features	Life status sensor (rare gas		
	and nitrogen only)		
	Bypass assembly		
	Surface mountable enclosure with cooling fan		
0 .: 1			

110 - 120 VAC or 220 - 240 VAC

	GASES PURIFIED		
Impurities removed	Rare gas	Nitrogen	Hydrogen
H ₂ O	<1 ppb	<1 ppb	<1 ppb
O ₂	<1 ppb	<1 ppb	<1 ppb
СО	<1 ppb	<1 ppb	<1 ppb
CO ₂	<1 ppb	<1 ppb	<1 ppb
Total hydrocarbons	<1 ppb	<1 ppb	N/A
H ₂	<1 ppb	<1 ppb	N/A
N ₂	<1 ppb	N/A	<1 ppb

PS4-MT50: Typical Flow Rate 30 – 100/150 slpm

SPECIFICATIONS

Maximum flow rate	150 slpm (hydrogen)
	100 slpm (nitrogen, helium, argon)
	30 slpm (xenon)
Outlet gas temperature	<50°C (122°F)
Average power consumption	1.1 kW
Metal particle filter	0.003 μm
Dimensions	Height: 113 cm (44.5")
	Width: 53 cm (21")
	Depth: 30 cm (12")
Weight	70 kg (154 lbs)
Standard features	High temperature alarm
	PLC controlled operation
	Exhausted enclosure with separate electronics bay
	Life status indicator
Optional features	N ₂ purge system (hydrogen model only)
	Hydrogen leak detector (hydrogen model only)
	Emergency off button
	Manual bypass
	110 – 120 VAC or 220 – 240 VAC

PERFORMANCE DATA

	GASES PURIFIED		
Impurities removed	Rare gas	Nitrogen	Hydrogen
H ₂ O	<1 ppb	<1 ppb	<1 ppb
O ₂	<1 ppb	<1 ppb	<1 ppb
СО	<1 ppb	<1 ppb	<1 ppb
CO ₂	<1 ppb	<1 ppb	<1 ppb
Total hydrocarbons	<1 ppb	<1 ppb	N/A
H ₂	<1 ppb	<1 ppb	N/A
N ₂	<1 ppb	N/A	<1 ppb

FOR MORE INFORMATION

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit <u>entegris.com</u> and select the <u>Contact Us</u> link to find the customer service center nearest you.

TERMS AND CONDITIONS OF SALE

All purchases are subject to Entegris' Terms and Conditions of Sale. To view and print this information, visit entegris.com and select the Terms and Conditions link in the footer.



Corporate Headquarters 129 Concord Road Billerica, MA 01821 USA

Customer Service

Tel +1 952 556 4181 Fax +1 952 556 8022 Toll Free 800 394 4083

Entegris®, the Entegris Rings Design®, and other product names are trademarks of Entegris, Inc. as listed on entegris.com/trademarks. All third-party product names, logos, and company names are trademarks or registered trademarks of their respective owners. Use of them does not imply any affiliation, sponsorship, or endorsement by the trademark owner.