

200 mm Wafer Storage Boxes

A variety of storage boxes to meet your 200 mm wafer handling requirements

Entegris is a leader in addressing automation, contamination control, and productivity requirements for today's 200 mm fabs. Our 200 mm wafer storage boxes offer outstanding protection and provide superior automated and manual handling. Thoughtful contamination control design features minimize particle generation.

Our portfolio comprises HA200 series, E99 series, and E210 series boxes with numerous options available to meet your specific application needs.

APPLICATIONS

- In-fab transport
- Fab wafer storage
- Process tool interface


FEATURES & BENEFITS

Automation compatible design	Enables convenient process tool interface
Thoughtful design features	Minimize particle generation from wafer chatter and carrier movement
Numerous material options available	Provide broad chemical compatibility
Stackable design	Allows for convenient, space-saving storage



HA200 SERIES

HA200 series storage boxes are the highest performance 200 mm storage boxes available, providing superior automated and manual handling. Design features minimize particle generation from wafer chatter and carrier movement.




HA200-0005 box

- Automation compatible
- Five-degree wafer tilt minimizes wafer chatter
- Single carrier capacity
- Accommodates select 25-capacity carriers, excluding wide-flange carriers
- EMSTAT™ AR base with EMSTAT AR or polycarbonate cover options
- Overall dimensions: 276 mm × 272 mm × 248 mm (10.9" × 10.7" × 9.8")

E99 SERIES

E99 series storage boxes are the industry standard, offering maximum stacking density for space limited stockers and work-in-process racks.




E99-111N-69F02 box

- Automation compatible
- Stackable
- Flat bottom
- Single carrier capacity
- Accommodates select 25-capacity wafer carriers, excluding wide-flange carriers
- STAT-PRO® 175 material with polycarbonate cover options
- Migration path compatible with STAT-PRO 100 material
- Overall dimensions: 285 mm × 272 mm × 241 mm (11.2" × 10.7" × 9.5")

E210 SERIES

E210 series storage boxes provide automation compatibility with wide-flange carriers and allow convenient manual handling. They incorporate features to minimize particle generation from wafer chatter and carrier movement.



E210-80-1000-69F02 box

- Automation compatible
- Stackable
- Seven-degree wafer tilt minimizes wafer chatter
- Balanced for easy manual handling
- Track notch registration
- Single carrier capacity
- Accommodates all 25- and 26-capacity wafer carriers
- STAT-PRO 175 material
- Overall dimensions: 302 mm × 272 mm × 292 mm (11.9" × 10.7" × 11.5")

ORDERING INFORMATION

Part number	Latch style	Compatible carriers	Travelers compatible	Material	Notes
E99-111N-69F02	Swing pin	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: STAT-PRO 175 Bottom: STAT-PRO 175 Latch: PBT	
E99-113N-69F02	Swing pin	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: STAT-PRO 175 Bottom: STAT-PRO 175 Latch: PBT	
E99-114N-PCPP-16	Swing pin	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: Clear polycarbonate Bottom: STAT-PRO 175 Latch: PBT	Red, blue, green and UV filtering amber polycarbonate covers available
E99-211N-69F02	Robotic	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: STAT-PRO 175 Bottom: STAT-PRO 175 Latch: Gray polycarbonate	
E99-213N-69F02	Robotic	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: STAT-PRO 175 Bottom: STAT-PRO 175 Latch: Gray polycarbonate	
E99-214N-PCPP-16	Robotic	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: Clear polycarbonate Bottom: STAT-PRO 175 Latch: Gray polycarbonate	Red, blue, green and UV filtering amber polycarbonate covers available
HA200-0002	Ergonomic	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: EMSTAT AR Bottom: EMSTAT AR Latch: Polycarbonate	Red, green and gray colored cover options are available
HA200-0005	Robotic	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: EMSTAT AR Bottom: EMSTAT AR Latch: Polycarbonate	Red, green and gray colored cover options are available
HA200-0063	Robotic	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: Amber polycarbonate Bottom: EMSTAT AR Latch: Polycarbonate	Red, blue, green and UV filtering amber polycarbonate covers available
E210-80-1000-69F02	Swing pin	All 25-capacity	No	Cover: STAT-PRO 175 Bottom: STAT-PRO 175 Latch: PBT	

ORDERING INFORMATION (CONTINUED)

Part number	Latch style	Compatible carriers	Travelers compatible	Material	Notes
E210-80-1000-PCPP	Swing pin	All 25-capacity	No	Cover: Clear polycarbonate Bottom: STAT-PRO 175 Latch: PBT	Red, blue, green and UV filtering amber polycarbonate covers available
E99-101-0603	Swing pin	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: Blue polypropylene Bottom: Blue polypropylene Latch: PBT	Red, green, yellow, white, natural, brown and orange colors available
E99-101-61C02	Swing pin	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: STAT-PRO 100 Bottom: STAT-PRO 100 Latch: PBT	
E99-101-69F02	Swing pin	192/198 series, 20X series and select 200 series* carriers	Yes	Cover: STAT-PRO 175 Bottom: STAT-PRO 175 Latch: PBT	

*Contact Entegris for ordering information.

OPTIONS

We offer a variety of options to tailor storage boxes to your specific applications.

Colored Box Covers


- Blue, green and gray STAT-PRO 175 and EMSTAT AR material covers available
- Red, blue, green and UV filtering amber polycarbonate covers available

Identification Options

- Laser marking
- Cardholders: E005-1-XXXX
- Hot stamping
- Colored ID tags
- Bar code labels

Flexible Traveler Envelopes

- Accommodate 127 mm × 216 mm (5.0" × 8.5") run travelers up to 3.2 mm (0.13") thick
- Compatible with select 200 mm storage boxes (see configurations)
- PVC material
- Part number: E96-1-1613 (for E99)
TR33-0100-P (for HA200)



E96-1-1613 on
E99-111N-69F02 storage box

MATERIAL SPECIFICATIONS

STAT-PRO 100

- Wafer transport carrier material
- Static dissipative blend of polypropylene and carbon powder
- Continuous use temperature limit: 55°C (131°F)

STAT-PRO 175 Material and EMSTAT AR Material

- High-performance storage box material
- Static dissipative blend of polypropylene and carbon fiber
- Colorable in cover applications
- Continuous use temperature limit: 55°C (131°F)

Polycarbonate

- Transparent storage box cover material
- Colorable (Red, blue, green, and UV filtering amber polycarbonate covers available)
- Continuous use temperature limit: 55°C (131°F)

FOR MORE INFORMATION

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit entegris.com and select the [Contact Us](#) link to find the customer service center nearest you.

TERMS AND CONDITIONS OF SALE

All purchases are subject to Entegris' Terms and Conditions of Sale. To view and print this information, visit entegris.com and select the [Terms and Conditions](#) link in the footer.



Corporate Headquarters

129 Concord Road
Billerica, MA 01821
USA

Customer Service

Tel +1 952 556 4181
Fax +1 952 556 8022
Toll Free 800 394 4083

Entegris®, the Entegris Rings Design®, and other product names are trademarks of Entegris, Inc. as listed on entegris.com/trademarks. All third-party product names, logos, and company names are trademarks or registered trademarks of their respective owners. Use of them does not imply any affiliation, sponsorship, or endorsement by the trademark owner.

©2001-2025 Entegris, Inc. | All rights reserved. | Printed in the USA | 1110-6136ENT-0925